



## Eaton 168637

Eaton Moeller series xEffect - FRCdM Type AC, A, U, R RCCB, 40A, 4p, 300mA, type S/A

□□□□

|                                 |                                                                  |
|---------------------------------|------------------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Moeller series<br>xEffect - FRCdM Type AC,<br>A, U, R RCCB |
| <b>CATALOG NUMBER</b>           | 168637                                                           |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 76 mm                                                            |
| <b>PRODUCT HEIGHT</b>           | 80 mm                                                            |
| <b>PRODUCT WIDTH</b>            | 70 mm                                                            |
| <b>PRODUCT WEIGHT</b>           | 0.32 kg                                                          |
| <b>COMPLIANCES</b>              | RoHS conform                                                     |
| <b>CERTIFICATIONS</b>           | IEC/EN 61008<br>EN45545-2<br>IEC 61373                           |

|                                                                                         |                                                                                                                                  |
|-----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| <b>USED WITH</b>                                                                        | FRCdM<br>Residual current circuit-breakers, digital<br>Type S/A                                                                  |
| <b>AMPERAGE RATING</b>                                                                  | 40 A                                                                                                                             |
| <b>FEATURES</b>                                                                         | Additional equipment possible<br>Residual current circuit-breakers, digital<br>Selective protection                              |
| <b>10.10 TEMPERATURE RISE</b>                                                           | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| <b>10.11 SHORT-CIRCUIT RATING</b>                                                       | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>                                              | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.13 MECHANICAL FUNCTION</b>                                                        | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| <b>10.2.2 CORROSION RESISTANCE</b>                                                      | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>                         | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>       | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b> | Meets the product standard's requirements.                                                                                       |
| <b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>                                 | Meets the product standard's requirements.                                                                                       |
| <b>10.2.5 LIFTING</b>                                                                   | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| <b>10.2.6 MECHANICAL</b>                                                                | Does not apply, since the                                                                                                        |

|                             |                                                                                                                                                                                                                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>CHARACTERISTIC CURVE</b> | <a href="#">eaton-current-xeffect-frcdm-rccb-characteristic-curve-03.jpg</a>                                                                                                                                                                                                         |
| <b>□□□</b>                  | <a href="#">eaton-current-xeffect-frcdm-rccb-wiring-diagram.jpg</a><br><a href="#">eaton-current-xeffect-frcdm-rccb-wiring-diagram-002.jpg</a><br><a href="#">eaton-xeffect-frcdm-rccb-wiring-diagram-003.jpg</a><br><a href="#">eaton-xeffect-frcdm-rccb-wiring-diagram-004.jpg</a> |
| <b>□□□□</b>                 | <a href="#">eaton-xeffect-digital-switchgear-brochure-br003004en-en-us.pdf</a>                                                                                                                                                                                                       |
| <b>□□</b>                   | <a href="#">eaton-current-xeffect-frcdm-rccb-dimensions.jpg</a>                                                                                                                                                                                                                      |

|                                                                 |                                                                                  |
|-----------------------------------------------------------------|----------------------------------------------------------------------------------|
| <b>IMPACT</b>                                                   | entire switchgear needs to be evaluated.                                         |
| <b>10.2.7 INSCRIPTIONS</b>                                      | Meets the product standard's requirements.                                       |
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated.               |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                                       |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.               |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.               |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                                           |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                                           |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                                           |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                                           |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                                           |
| <b>FITTED WITH:</b>                                             | Interlocking device                                                              |
| <b>FRAME</b>                                                    | 45 mm                                                                            |
| <b>FREQUENCY RATING</b>                                         | 50 Hz                                                                            |
| <b>POLLUTION DEGREE</b>                                         | 2                                                                                |
| <b>MOUNTING METHOD</b>                                          | Quick attachment with 2 latch positions for DIN-rail<br>IEC/EN 60715<br>DIN rail |
| <b>CLIMATIC PROOFING</b>                                        | 25-55 °C / 90-95% relative humidity according to IEC 60068-2                     |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>            | 6.2 W                                                                            |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 4 kV                                                                             |
| <b>ADMISSIBLE BACK-UP FUSE</b>                                  | 63 A gG/gL                                                                       |
| <b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>                 | 10 kA                                                                            |
| <b>ADMISSIBLE BACK-UP</b>                                       | 40 A gG/gL                                                                       |

|                                                                            |                                                   |
|----------------------------------------------------------------------------|---------------------------------------------------|
| <b>FUSE OVERLOAD - MAX</b>                                                 |                                                   |
| <b>BUILT-IN WIDTH<br/>(NUMBER OF UNITS)</b>                                | 70 mm (4 SU)                                      |
| <b>BUSBAR MATERIAL<br/>THICKNESS</b>                                       | 0.8 mm - 2 mm                                     |
| <b>SHORT-CIRCUIT RATING</b>                                                | 63 A (max. admissible<br>back-up fuse)            |
| <b>STATUS INDICATION</b>                                                   | White / blue                                      |
| <b>SWITCHING CAPACITY OF<br/>AUXILIARY CONTACT -<br/>MIN</b>               | 10 $\mu$ A, 10 mV DC                              |
| <b>TERMINAL PROTECTION</b>                                                 | Finger and hand touch<br>safe, DGUV VS3, EN 50274 |
| <b>TERMINALS (TOP AND<br/>BOTTOM)</b>                                      | Twin-purpose terminals                            |
| <b>TEST CIRCUIT RANGE</b>                                                  | 196 V AC - 456 V AC                               |
| <b>AMBIENT OPERATING<br/>TEMPERATURE - MAX</b>                             | 60 °C                                             |
| <b>AMBIENT OPERATING<br/>TEMPERATURE - MIN</b>                             | -25 °C                                            |
| <b>BUILT-IN DEPTH</b>                                                      | 70.5 mm                                           |
| <b>CONNECTABLE<br/>CONDUCTOR CROSS<br/>SECTION (MULTI-WIRED)<br/>- MAX</b> | 16 mm <sup>2</sup>                                |
| <b>CONNECTABLE<br/>CONDUCTOR CROSS<br/>SECTION (MULTI-WIRED)<br/>- MIN</b> | 1.5 mm <sup>2</sup>                               |
| <b>CONNECTABLE<br/>CONDUCTOR CROSS<br/>SECTION (SOLID-CORE) -<br/>MAX</b>  | 35 mm <sup>2</sup>                                |
| <b>CONNECTABLE<br/>CONDUCTOR CROSS<br/>SECTION (SOLID-CORE) -<br/>MIN</b>  | 1.5 mm <sup>2</sup>                               |
| <b>FAULT CURRENT RATING</b>                                                | 300 mA                                            |
| <b>HEAT DISSIPATION<br/>CAPACITY</b>                                       | 6.2 W                                             |
| <b>HEAT DISSIPATION PER<br/>POLE, CURRENT-<br/>DEPENDENT</b>               | 0 W                                               |
| <b>INTERNAL RESISTANCE<br/>AT ROOM TEMPERATURE<br/>AND 50HZ</b>            | 0.64 m $\Omega$                                   |
| <b>PERMITTED STORAGE<br/>AND TRANSPORT<br/>TEMPERATURE - MAX</b>           | 60 °C                                             |
| <b>PERMITTED STORAGE<br/>AND TRANSPORT</b>                                 | -35 °C                                            |

|                                  |                                            |
|----------------------------------|--------------------------------------------|
| <b>TEMPERATURE - MIN</b>         |                                            |
| <b>CONTACT POSITION</b>          | Red / green                                |
| <b>INDICATOR COLOR</b>           |                                            |
| <b>MOUNTING POSITION</b>         | As required                                |
| <b>LIFESPAN, MECHANICAL</b>      | 20000 operations                           |
| <b>DEGREE OF PROTECTION</b>      | IP20, IP40 with suitable enclosure<br>IP20 |
| <b>IMPULSE WITHSTAND CURRENT</b> | 5 kA (8/20 µs) surge-proof                 |
| <b>NUMBER OF POLES</b>           | Four-pole                                  |
| <b>LEAKAGE CURRENT TYPE</b>      | A                                          |
| <b>LIFESPAN, ELECTRICAL</b>      | 4000 operations                            |

|             |                                                                                                                                     |
|-------------|-------------------------------------------------------------------------------------------------------------------------------------|
| <b>TYPE</b> | <ul style="list-style-type: none"> <li>• FRCdM</li> <li>• Residual current circuit-breakers, digital</li> <li>• Type S/A</li> </ul> |
|-------------|-------------------------------------------------------------------------------------------------------------------------------------|

|                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>SPECIAL FEATURES</b> | <ul style="list-style-type: none"> <li>• Current test marks as per inscription</li> <li>• Dry auxiliary contact: &gt; 100,000 electrical switching operations per minute at 2 A 30 VDC resistive load</li> <li>• Dry auxiliary contact: &gt; 5 x 100,000 electrical switching operations per minute at 1 A 30 VDC resistive load</li> <li>• Maximum operating temperature is 60 °C: Starting at 40 °C, the max. permissible continuous current decreases by 2.5% for every 1 °C</li> </ul> |
|-------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                    |                                                                          |
|--------------------|--------------------------------------------------------------------------|
| <b>APPLICATION</b> | xEffect - Switchgear for industrial and advanced commercial applications |
|--------------------|--------------------------------------------------------------------------|

|                         |                         |
|-------------------------|-------------------------|
| <b>SENSITIVITY TYPE</b> | Pulse-current sensitive |
|-------------------------|-------------------------|

|                                  |                                                                  |
|----------------------------------|------------------------------------------------------------------|
| <b>TERMINAL CAPACITY (CABLE)</b> | M5 (with cross-recessed screw as defined in EN ISO 4757-Z2, PZ2) |
|----------------------------------|------------------------------------------------------------------|

|                                  |       |
|----------------------------------|-------|
| <b>RATED FAULT CURRENT - MAX</b> | 0.3 A |
|----------------------------------|-------|

|                                                                                   |                                                              |
|-----------------------------------------------------------------------------------|--------------------------------------------------------------|
| <b>RATED FAULT CURRENT - MIN</b>                                                  | 0.3 A                                                        |
| <b>RATED INSULATION VOLTAGE (UI)</b>                                              | 440 V                                                        |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>              | 40 A                                                         |
| <b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>                                       | 415 V                                                        |
| <b>RATED RESIDUAL MAKING AND BREAKING CAPACITY</b>                                | 500 A                                                        |
| <b>RATED SWITCHING CAPACITY (RESISTIVE LOAD) OF AUXILIARY CONTACT AT 240 V AC</b> | 0.25 A                                                       |
| <b>RATED SWITCHING CAPACITY (RESISTIVE LOAD) OF AUXILIARY CONTACT AT 30 V DC</b>  | 2 A                                                          |
| <b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>                             | 0 W                                                          |
| <b>SURGE CURRENT CAPACITY</b>                                                     | 5 kA                                                         |
| <b>SWITCHING CURRENT OF AUXILIARY CONTACT - MAX</b>                               | 2 A                                                          |
| <b>SWITCHING DUTY WITH RESISTIVE LOAD OF AUXILIARY CONTACT - MAX</b>              | 60 W                                                         |
| <b>SWITCHING VOLTAGE AT AC OF AUXILIARY CONTACT - MAX</b>                         | 240 V                                                        |
| <b>SWITCHING VOLTAGE AT DC OF AUXILIARY CONTACT - MAX</b>                         | 220 V                                                        |
| <b>VOLTAGE RATING - MAX</b>                                                       | 264 VAC                                                      |
| <b>VOLTAGE RATING - MIN</b>                                                       | 50 VAC                                                       |
| <b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>                                        | 4                                                            |
| <b>VOLTAGE RATING (IEC/EN 60947-2)</b>                                            | 240 V AC / 415 V AC                                          |
| <b>VOLTAGE TYPE</b>                                                               | AC                                                           |
| <b>TERMINAL CAPACITY (SOLID WIRE)</b>                                             | 1.5 mm <sup>2</sup> - 35 mm <sup>2</sup>                     |
| <b>TRIPPING TIME</b>                                                              | Selective switch off<br>40 ms delayed - selective switch off |
| <b>RATED SHORT-CIRCUIT</b>                                                        | 10 kA                                                        |

|                                           |                    |
|-------------------------------------------|--------------------|
| STRENGTH                                  |                    |
| TIGHTENING TORQUE                         | 2 Nm - 2.4 Nm      |
| TERMINAL CAPACITY<br>(STRANDED CABLE)     | 16 mm² (2x)        |
| TERMINAL CAPACITY OF<br>AUXILIARY CONTACT | 0.25 mm² - 1.5 mm² |
| RAL-NUMBER                                | 7035               |
| COLOR                                     | Gray               |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,  Eaton.com

© 2025  

Follow us on social media to get the latest product and support information.

