



## Eaton 168692

SPET2-280/3. Surge arrester complete, 3-pole, 280VAC, 3x10kA

□□□□

<b>PRODUCT NAME</b>	Eaton Distribution parts
<b>CATALOG NUMBER</b>	168692
<b>PRODUCT LENGTH/DEPTH</b>	86 mm
<b>PRODUCT HEIGHT</b>	69 mm
<b>PRODUCT WIDTH</b>	52.5 mm
<b>PRODUCT WEIGHT</b>	0.275 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	CE



Powering Business Worldwide

□□□□

<b>FEATURES</b>	Category type 2
<b>FRAME</b>	3 modular spacing
<b>DEGREE OF PROTECTION</b>	IP20
<b>MOUNTING METHOD</b>	DIN rail (top hat rail) 35 mm
<b>SIGNALLING AT THE DEVICE</b>	Optic
<b>SYSTEM CONFIGURATION TYPE</b>	Other TN TN-S
<b>TYPE</b>	Surge arrester
<b>APPLICATION</b>	Open areas Residential buildings Utility buildings
<b>CONDUCTOR CROSS SECTION (SOLID, SOLID-STRAND) - MAX</b>	25 mm <sup>2</sup>
<b>CONDUCTOR CROSS SECTION (SOLID, SOLID-STRAND) - MIN</b>	25 mm <sup>2</sup>
<b>CONTINUOUS VOLTAGE AT AC - MAX</b>	280 V
<b>DISCHARGE SURGE CURRENT (8/20) - MAX</b>	20 kA
<b>NOMINAL DISCHARGE SURGE CURRENT (8/20)</b>	10 kA
<b>NOMINAL VOLTAGE AT AC</b>	280 V
<b>NUMBER OF CONDUCTORS WITHOUT EARTHING</b>	3
<b>VOLTAGE PROTECTION LEVEL</b>	1.2 KV
<b>OVERCURRENT PROTECTION DEVICE, SERIES CONNECTION (FUSE) - MAX</b>	100 A

□□

<b>CHARACTERISTIC CURVE</b>	<a href="#">eaton-dimensions-mas_spb12.jpg</a>
<b>PEP ECO-PASSPORT</b>	<a href="#">eaton-t2-arrestor-pep-eato-00260-v0101-en.pdf</a>
<b>□□□</b>	<a href="#">eaton-xpole-spct2-surge-protection-device-wiring-diagram-003.jpg</a>

