



□□□□□

## Eaton 163807

Eaton Distribution parts. Fuse switch  
disconnecter, 4p, NH00, AC22, 41C071BMC

□□□□

|                                 |                          |
|---------------------------------|--------------------------|
| <b>PRODUCT NAME</b>             | Eaton Distribution parts |
| <b>CATALOG NUMBER</b>           | 163807                   |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 590 mm                   |
| <b>PRODUCT HEIGHT</b>           | 99.5 mm                  |
| <b>PRODUCT WIDTH</b>            | 280 mm                   |
| <b>PRODUCT WEIGHT</b>           | 8.88 kg                  |
| <b>COMPLIANCES</b>              | RoHS conform             |

□□□□

□□

|          |                      |
|----------|----------------------|
| FEATURES | Motor drive optional |
|----------|----------------------|

|              |                                |
|--------------|--------------------------------|
| FITTED WITH: | Connectors<br>Error protection |
|--------------|--------------------------------|

|                                                       |      |
|-------------------------------------------------------|------|
| RATED OPERATIONAL<br>POWER AT AC-23A, 400 V,<br>50 HZ | 0 kW |
|-------------------------------------------------------|------|

|                                 |       |
|---------------------------------|-------|
| RATED PERMANENT<br>CURRENT (IU) | 160 A |
|---------------------------------|-------|

|                                     |       |
|-------------------------------------|-------|
| RATED UNINTERRUPTED<br>CURRENT (IU) | 160 A |
|-------------------------------------|-------|

|                                                  |       |
|--------------------------------------------------|-------|
| CONDITIONED RATED<br>SHORT-CIRCUIT CURRENT<br>IQ | 55 kA |
|--------------------------------------------------|-------|

|                          |     |
|--------------------------|-----|
| WITH ERROR<br>PROTECTION | Yes |
|--------------------------|-----|

|                 |           |
|-----------------|-----------|
| NUMBER OF POLES | Four-pole |
|-----------------|-----------|

|                                          |      |
|------------------------------------------|------|
| RATED OPERATION<br>POWER AT AC-23, 400 V | 0 kW |
|------------------------------------------|------|

|                                                |      |
|------------------------------------------------|------|
| RATED SHORT-TIME<br>WITHSTAND CURRENT<br>(ICW) | 0 kA |
|------------------------------------------------|------|

|                                                  |                  |
|--------------------------------------------------|------------------|
| ELECTRICAL<br>CONNECTION TYPE OF<br>MAIN CIRCUIT | Screw connection |
|--------------------------------------------------|------------------|

|                   |            |
|-------------------|------------|
| ACTUATOR POSITION | Front side |
|-------------------|------------|

|               |                     |
|---------------|---------------------|
| ACTUATOR TYPE | Long turning handle |
|---------------|---------------------|

|              |                |
|--------------|----------------|
| SUITABLE FOR | Front mounting |
|--------------|----------------|

|                                                    |       |
|----------------------------------------------------|-------|
| RATED CONDITIONAL<br>SHORT-CIRCUIT CURRENT<br>(IQ) | 55 kA |
|----------------------------------------------------|-------|

|                    |      |
|--------------------|------|
| SUITABLE FOR FUSES | NH00 |
|--------------------|------|

|                  |      |
|------------------|------|
| CABLE ENTRY TYPE | Side |
|------------------|------|

|                                      |      |
|--------------------------------------|------|
| DEGREE OF PROTECTION<br>(FRONT SIDE) | IP40 |
|--------------------------------------|------|

|                                 |      |
|---------------------------------|------|
| POWER RATING AT AC-23,<br>400 V | 0 kW |
|---------------------------------|------|

|                                                |       |
|------------------------------------------------|-------|
| RATED OPERATING<br>VOLTAGE (UE) AT AC -<br>MAX | 690 V |
|------------------------------------------------|-------|

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

