



□□□□□

## Eaton 168858

Eaton Distribution parts. Phase busbar, N,  
10qmm, pin, 1m, 1,5MU

□□□□

<b>PRODUCT NAME</b>	Eaton Distribution parts
<b>CATALOG NUMBER</b>	168858
<b>PRODUCT LENGTH/DEPTH</b>	1012 mm
<b>PRODUCT HEIGHT</b>	35 mm
<b>PRODUCT WIDTH</b>	7 mm
<b>PRODUCT WEIGHT</b>	0.205 kg
<b>COMPLIANCES</b>	RoHS conform

## □□□□

<b>USED WITH</b>	BB-EV Busbar
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• BB-EV</li> <li>• Busbar</li> </ul>
<b>FEATURES</b>	Insulated Can be cut to size
<b>ACCESSORY/SPARE PART TYPE</b>	Busbar for miniature circuit breaker Busbar for TVSS Busbar for combined residual current/power circuit breaker Busbar for residual current circuit breakers
<b>ELECTRIC CONNECTION TYPE</b>	Pin
<b>RATED SURGE VOLTAGE</b>	4.5 kV
<b>RATED UNINTERRUPTED CURRENT (IU)</b>	63 A
<b>SUITABLE FOR NUMBER OF DEVICES</b>	6
<b>APPLICATION</b>	Switchgear for industrial and advanced commercial applications
<b>NUMBER OF POLES</b>	Two-pole
<b>COLOR</b>	Other
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	0 kA
<b>CROSS SECTION</b>	10 mm <sup>2</sup>
<b>NUMBER OF MODULAR SPACINGS</b>	1.5
<b>NUMBER OF PHASES</b>	1
<b>PITCH DIMENSIONS</b>	27 mm
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	690 V
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	0 kA
<b>FUNCTIONS</b>	Busbar
<b>SUITABLE FOR</b>	Devices with N-busbar

## □□

□□□	<a href="#">eaton-wiring-diagram-versch.jpg</a>
□□	<a href="#">eaton-dimensions-mas-zv7-50a.jpg</a>

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

