



□□□□

## Eaton 165466

RCD/MCB, 4A, 100mA, miniature circuit-breaker trip curve B, 1 pole+N, residual current circuit-breaker trip characteristic: AC (PFL4-4/1N/B/01)

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xPole - PFL4 RCBO - residual-current circuit breaker with overcurrent protection
<b>CATALOG NUMBER</b>	165466
<b>PRODUCT LENGTH/DEPTH</b>	86 mm
<b>PRODUCT HEIGHT</b>	75 mm
<b>PRODUCT WIDTH</b>	37 mm
<b>PRODUCT WEIGHT</b>	0.207 kg
<b>COMPLIANCES</b>	RoHS conform CE Marked



Powering Business Worldwide

□□□□

<b>VOLTAGE RATING</b>	230 V
<b>SURGE CURRENT CAPACITY</b>	0.25 kA
<b>VOLTAGE TYPE</b>	AC
<b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>	2
<b>FEATURES</b>	Concurrently switching N-neutral
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.

□□

□□□□□	<a href="#">eaton-mcb-rccb-rcbo-g9-il019140zu.pdf</a>
□□□□	<a href="#">eaton-xpole-pfl4-rcbo-catalog-ca019047en-en-us.pdf</a>

<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>OPERATING AMBIENT TEMPERATURE - MAX</b>	40 °C
<b>OPERATING AMBIENT TEMPERATURE - MIN</b>	-25 °C
<b>RATED CURRENT</b>	4 A
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	4 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>	0 W
<b>BUILT-IN DEPTH</b>	69.5 mm
<b>CURRENT LIMITING CLASS</b>	3
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60947-2)</b>	0 kA
<b>FAULT CURRENT RATING</b>	0.1 A
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>	0 W
<b>NUMBER OF POLES (PROTECTED)</b>	1

