

Eaton 169392

Eaton DA1 Variable frequency drive, 400 V AC, 3-phase, 39 A, 18.5 kW, IP55/NEMA 12, Radio interference suppression filter, OLED display

PRODUCT NAME	Eaton DA1 Variable frequency drive
CATALOG NUMBER	169392
PRODUCT LENGTH/DEPTH	240 mm
PRODUCT HEIGHT	450 mm
PRODUCT WIDTH	173 mm
PRODUCT WEIGHT	11.5 kg
CERTIFICATIONS	CE DNV UkrSEPRO UL UL Category Control No.: NMMS, NMMS7 UL 508C IEC/EN61800-3 CUL IEC/EN61800-5 RCM Safety: EN 61800-5-1: 2003
	EAC RoHS, ISO 9001 UL File No.: E172143 CSA-C22.2 No. 14 IEC/EN 61800-3 Certified by UL for use in Canada Specification for general requirements: IEC/EN 61800-2 UL report applies to both US and Canada
CATALOG NOTES	The brake resistors are assigned based on the maximum rated power of the variable frequency

drive. Additional brake resistors and designs (e.g. different duty cycles) are available upon request.

PRODUCT CATEGORY	Variable frequency drives
FEATURES	Parameterization: Fieldbus
	Parameterization: Keypad
	Parameterization: drivesConnect
	Parameterization: drivesConnect mobile (App)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.

INSTALLATION VIDEOS	Video PowerXL DA1
	eaton-powerxl-variable-frequency-drives-dc1-da1-brochure-br040001en-en-us.pdf
	eaton-powerxl-da1-installation-manual-mn04020005z-en-us.pdf
	eaton-powerxl-da1-application-manual-mn04020006z-en-us.pdf
	eaton-frequency-inverter-dimensions-023.eps
	eaton-frequency-inverter-3d-drawing-014.eps

10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Brake chopper Internal DC link Additional PCB protection Breaking resistance OLED display Control unit Radio interference suppression filter IGBT inverter PC connection
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	Yes In conjunction with DX-NET-SWD1 SmartWire DT module
OPERATING MODE	Sensorless vector control (SLV) Speed control with slip compensation

	Optional: Vector control with feedback (CLV) U/f control
FRAME SIZE	FS4
ALTITUDE	Max. 1000 m Max. 4000 m Above 1000 m with 1 % derating per 100 m
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 30 seconds
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	40 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	60 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 400 V	27.02 kVA
APPARENT POWER AT 480 V	32.42 kVA
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	36 A
MOUNTING POSITION	Vertical
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3,

	VBG4)
RESOLUTION	0.1 Hz (Frequency resolution, setpoint value)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	780 VDC
VOLTAGE RATING - MAX	480 VAC
COMMUNICATION INTERFACE	Ethernet IP, optional PROFINET, optional SmartWire-DT, optional PROFIBUS, optional OP-Bus (RS485), built in CANopen®, built in DeviceNet, optional Modbus-TCP, optional Modbus RTU, built in EtherCAT, optional
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	NEMA 12 IP55
PROTOCOL	MODBUS PROFIBUS CAN PROFINET IO Other bus systems EtherNet/IP DeviceNet TCP/IP
ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD	34 A
SYSTEM CONFIGURATION TYPE	AC supply systems with earthed center point
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	25 HP
BRAKING RESISTANCE	22 Ω
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	444 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER	0 W

POLE, CURRENT-DEPENDENT PVID	
INPUT CURRENT ILN AT 150% OVERLOAD	44.1 A
BRAKING TORQUE	Max. 100 % of rated operational current I _e , variable, DC - Main circuit Max. 30 % MN, Standard - Main circuit Max. 100 % of rated operational current I _e with external braking resistor - Main circuit
CABLE LENGTH	C3 ≤ 25 m, Radio interference level, maximum motor cable length 300 m, unscreened, with motor choke, maximum permissible, Motor feeder 100 m, screened, maximum permissible, Motor feeder 150 m, unscreened, maximum permissible, Motor feeder C2 ≤ 5 m, Radio interference level, maximum motor cable length 200 m, screened, with motor choke, maximum permissible, Motor feeder
FUNCTIONS	4-quadrant operation possible
OUTPUT VOLTAGE (U2)	480 V AC, 3-phase 400 V AC, 3-phase
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	5
RADIO INTERFERENCE CLASS	Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters

	(optional) may be necessary.
NUMBER OF OUTPUTS (DIGITAL)	2
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), for 4 seconds every 40 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	2 (parameterizable, 1 N/O and 1 changeover contact, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	444 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 10 mA)
EFFICIENCY	97.6 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 100 mA)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	2.47 mA
MAINS VOLTAGE - MAX	480 V
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I2N	39 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	0
NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES	0

(PROFINET)	
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	18.5 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	18.5 kW
OUTPUT FREQUENCY - MAX	500 Hz
OUTPUT FREQUENCY - MIN	0 Hz
OUTPUT VOLTAGE - MAX	500 V
OVERLOAD CURRENT I_L AT 150% OVERLOAD	58.5 A
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	8 kHz, 4 - 24 kHz adjustable (audible), fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	480 V AC, 3-phase 400 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	60 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
RATED FREQUENCY - MAX	62 Hz
RATED FREQUENCY - MIN	48 Hz
RATED OPERATIONAL CURRENT (I_E) AT 150% OVERLOAD	39 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (I_N)	39 A
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE	18.5 kW
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL2, PLc Cat 2)
HEAT DISSIPATION AT CURRENT/SPEED	178 W at 25% current and 0% speed 205 W at 25% current and 50% speed 221 W at 50% current and 0% speed 246 W at 50% current and 50% speed

296 W at 50% current and
90% speed
371 W at 100% current
and 0% speed
428 W at 100% current
and 50% speed
504 W at 100% current
and 90% speed

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the
latest product and support
information.

