



Eaton 167580

Eaton Moeller series xPole - SPCT2 Surge Protection Device. Plug-in surge arresters, 3p, 75VAC, 3x20kA

□□□□

PRODUCT NAME	Eaton Moeller series xPole - SPCT2 Surge protection device
CATALOG NUMBER	167580
PRODUCT LENGTH/DEPTH	85 mm
PRODUCT HEIGHT	67 mm
PRODUCT WIDTH	52.5 mm
PRODUCT WEIGHT	0.287 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	CE

0000

FEATURES	Category type 2
FRAME	3 modular spacing
DEGREE OF PROTECTION	IP20
MOUNTING METHOD	DIN rail (top hat rail) 35 mm
VOLTAGE PROTECTION LEVEL (L-N)	0 kV
VOLTAGE PROTECTION LEVEL (N-PE)	0 kV
SIGNALLING AT THE DEVICE	Optic
SYSTEM CONFIGURATION TYPE	TN Other
TYPE	Surge arrester
APPLICATION	Open areas Residential buildings Utility buildings
CONDUCTOR CROSS SECTION (FLEXIBLE, FINE-STRAND) - MAX	35 mm ²
CONDUCTOR CROSS SECTION (FLEXIBLE, FINE-STRAND) - MIN	35 mm ²
CONDUCTOR CROSS SECTION (SOLID, SOLID-STRAND) - MAX	25 mm ²
CONDUCTOR CROSS SECTION (SOLID, SOLID-STRAND) - MIN	25 mm ²
CONTINUOUS VOLTAGE AT AC - MAX	75 V
CONTINUOUS VOLTAGE AT DC - MAX	0 V
DISCHARGE SURGE CURRENT (8/20) - MAX	30 kA
NOMINAL DISCHARGE SURGE CURRENT (8/20)	15 kA
NOMINAL VOLTAGE AT AC	75 V
NOMINAL VOLTAGE AT DC	0 V
NUMBER OF CONDUCTORS WITHOUT EARTHING	3
PV-VOLTAGE - MAX	0 V
SHORT-CIRCUIT BREAKING CAPACITY (ISCCR)	0 kA
VOLTAGE PROTECTION	0.55 kV

00

000	eaton-xpole-spct2-surge-protection-device-wiring-diagram-003.jpg
0000	eaton-spct2-surge-protection-catalog-ca010005en-en-us.pdf
00	eaton-xpole-spct2-surge-protection-device-dimensions.jpg

LEVEL	
OVERCURRENT PROTECTION DEVICE, PARALLEL CONNECTION (FUSE) - MAX	0 A
OVERCURRENT PROTECTION DEVICE, SERIES CONNECTION (FUSE) - MAX	125 A
INTEGRATED SHORT-CIRCUIT PROTECTION SELECTIVE TO FUSE GG	0 A
