



□□□□

Eaton 168151

Digital residual current circuit-breaker/miniature circuit-breaker, 25A, 100mA, miniature circuit-breaker trip curve: D, 1pole+N, residual current circuit-breaker trip characteristic: G/A. dRBM-25/1N/D/01-G/A

□□□□

PRODUCT NAME	Eaton Moeller series xPole - dRBM RCBO - residual-current circuit breaker with overcurrent protection
CATALOG NUMBER	168151
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	35 mm
PRODUCT WEIGHT	0.23 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CE



Powering Business Worldwide

□□□□

VOLTAGE RATING	240 V - 240 V
SURGE CURRENT CAPACITY	3 kA
VOLTAGE TYPE	AC
WIDTH IN NUMBER OF MODULAR SPACINGS	2
FEATURES	Anti- nuisance tripping version Concurrently switching N- neutral
OPERATING AMBIENT TEMPERATURE - MAX	40 °C
OPERATING AMBIENT TEMPERATURE - MIN	-25 °C
RATED CURRENT	25 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	25 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
BUILT-IN DEPTH	75 mm
CURRENT LIMITING CLASS	3
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60947-2)	0 kA
FAULT CURRENT RATING	0.1 A
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
NUMBER OF POLES (PROTECTED)	1
NUMBER OF POLES (TOTAL)	2
BASIC FUNCTION	Combined RCD/MCB devices
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	4.2 W
DEGREE OF PROTECTION	IP20
OVERVOLTAGE CATEGORY	III
POLLUTION DEGREE	2
LEAKAGE CURRENT TYPE	A
RELEASE	D

□□

□□□□

[eaton-xpole-drbm-rdbo-catalog-ca019063en-en-us.pdf](https://www.eaton.com/content/dam/eaton/products/circuit-breakers/molded-case-breakers/mccb/eaton-xpole-drbm-rdbo-catalog-ca019063en-en-us.pdf)

