



□□□□□

Eaton 168455

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 400A, plug-in module, C3-S400-SVE

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker magnetic
CATALOG NUMBER	168455
PRODUCT LENGTH/DEPTH	335 mm
PRODUCT HEIGHT	215.2 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	6.38 kg
COMPLIANCES	RoHS conform

□□□□

AMPERAGE RATING	400 A
VOLTAGE RATING	690 V - 690 V
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND	Meets the product

□□

CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-035.eps
□□□□□	eaton-circuit-breaker-plug-in-adapter-nzm2-il01219023z.pdf

CREEPAGE DISTANCES	standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
MOUNTING METHOD	Built-in device plug-in technique
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	72.48 W
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
RATED OPERATING POWER AT AC-3, 230 V	132 kW
RATED OPERATING POWER AT AC-3, 400 V	200 kW
SWITCH OFF TECHNIQUE	Magnetic
DEGREE OF PROTECTION	IP20
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
RATED OPERATIONAL CURRENT	349 A (400 V AC-3)
NUMBER OF POLES	Three-pole
TYPE	Circuit breaker
SPECIAL FEATURES	• Motor protection in

- conjunction with overload relay
- With short-circuit release
- Without overload release I_r
- IEC/EN 60947-4-1, IEC/EN 60947-2
- The circuit-breaker fulfills all requirements for AC-3 switching category.
- Rated current = rated uninterrupted current: 400 A

SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	5000 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	2800 A
HANDLE TYPE	Rocker lever
INSTANTANEOUS CURRENT SETTING (II) - MAX	44328 A
INSTANTANEOUS CURRENT SETTING (II) - MIN	7 A
OVERLOAD CURRENT SETTING (IR) - MAX	0 A
OVERLOAD CURRENT SETTING (IR) - MIN	0 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	36 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	36 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ	36 kA

