



## Eaton 170457

Eaton Moeller series xEffect - FRCmM Type AC, A, U, R RCCB. Residual current circuit breaker (RCCB), 100A, 4p, 30mA, type U

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller series xEffect - FRCmM Type AC, A, U, R RCCB
<b>CATALOG NUMBER</b>	170457
<b>PRODUCT LENGTH/DEPTH</b>	80 mm
<b>PRODUCT HEIGHT</b>	76 mm
<b>PRODUCT WIDTH</b>	70 mm
<b>PRODUCT WEIGHT</b>	0.386 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	IEC/EN 61008



Powering Business Worldwide

**USED WITH**

Residual current circuit  
breakers  
Type U  
FRCmM

**AMPERAGE RATING**

100 A

**FEATURES**

Additional equipment  
possible  
Residual current circuit  
breaker

**10.10 TEMPERATURE RISE**

The panel builder is  
responsible for the  
temperature rise  
calculation. Eaton will  
provide heat dissipation  
data for the devices.

**10.11 SHORT-CIRCUIT  
RATING**

Is the panel builder's  
responsibility. The  
specifications for the  
switchgear must be  
observed.

**10.12 ELECTROMAGNETIC  
COMPATIBILITY**

Is the panel builder's  
responsibility. The  
specifications for the  
switchgear must be  
observed.

**10.13 MECHANICAL  
FUNCTION**

The device meets the  
requirements, provided  
the information in the  
instruction leaflet (IL) is  
observed.

**10.2.2 CORROSION  
RESISTANCE**

Meets the product  
standard's requirements.

**10.2.3.1 VERIFICATION OF  
THERMAL STABILITY OF  
ENCLOSURES**

Meets the product  
standard's requirements.

**10.2.3.2 VERIFICATION OF  
RESISTANCE OF  
INSULATING MATERIALS  
TO NORMAL HEAT**

Meets the product  
standard's requirements.

**10.2.3.3 RESIST. OF  
INSUL. MAT. TO  
ABNORMAL HEAT/FIRE  
BY INTERNAL ELECT.  
EFFECTS**

Meets the product  
standard's requirements.

**10.2.4 RESISTANCE TO  
ULTRA-VIOLET (UV)  
RADIATION**

Meets the product  
standard's requirements.

**10.2.5 LIFTING**

Does not apply, since the  
entire switchgear needs to  
be evaluated.

**10.2.6 MECHANICAL  
IMPACT**

Does not apply, since the  
entire switchgear needs to

[eaton-circuit-breaker-  
xeffect-frcmm-rccb-  
dimensions.jpg](#)

	be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Interlocking device
<b>FRAME</b>	45 mm
<b>FREQUENCY RATING</b>	50 Hz / 60 Hz 50 Hz
<b>POLLUTION DEGREE</b>	2
<b>LIFESPAN, MECHANICAL</b>	20000 operations
<b>MOUNTING METHOD</b>	Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715 DIN rail
<b>CLIMATIC PROOFING</b>	25-55 °C / 90-95% relative humidity according to IEC 60068-2
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	18.8 W
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4 kV 4 kV (1.2/50 µ s)
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	10 kA
<b>ADMISSIBLE BACK-UP FUSE OVERLOAD - MAX</b>	80 A gG/gL

<b>BUILT-IN WIDTH (NUMBER OF UNITS)</b>	70 mm (4 SU)
<b>BUSBAR MATERIAL THICKNESS</b>	0.8 mm - 2 mm
<b>SHORT-CIRCUIT RATING</b>	100 A (max. admissible back-up fuse)
<b>STATUS INDICATION</b>	White / blue
<b>TERMINAL PROTECTION</b>	Finger and hand touch safe, DGUV VS3, EN 50274
<b>TERMINALS (TOP AND BOTTOM)</b>	Twin-purpose terminals
<b>TEST CIRCUIT RANGE</b>	196 V AC - 264 V AC
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	75 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>BUILT-IN DEPTH</b>	70.5 mm
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>	16 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>	1.5 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>	35 mm <sup>2</sup>
<b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>	1.5 mm <sup>2</sup>
<b>FAULT CURRENT RATING</b>	30 mA
<b>HEAT DISSIPATION CAPACITY</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT</b>	4.7 W
<b>PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MAX</b>	60 °C
<b>PERMITTED STORAGE AND TRANSPORT TEMPERATURE - MIN</b>	-35 °C
<b>CONTACT POSITION INDICATOR COLOR</b>	Red / green
<b>MOUNTING POSITION</b>	As required
<b>DEGREE OF PROTECTION</b>	IP20 IP20, IP40 with suitable enclosure

<b>IMPULSE WITHSTAND CURRENT</b>	3 kA (8/20 µs) surge-proof
<b>NUMBER OF POLES</b>	Four-pole
<b>LEAKAGE CURRENT TYPE</b>	A
<b>LIFESPAN, ELECTRICAL</b>	4000 operations
<b>TYPE</b>	<ul style="list-style-type: none"> <li>• FRCmM</li> <li>• Residual current circuit breakers</li> <li>• Type U</li> </ul>
<b>SPECIAL FEATURES</b>	<ul style="list-style-type: none"> <li>• Current test marks as per inscription</li> <li>• Maximum operating temperature is 75 °C: Starting at 40 °C, the max. permissible continuous current decreases by 1.2% for every 1 °C</li> </ul>
<b>APPLICATION</b>	Residual current circuit breaker - frequency converter-proof
<b>FUNCTIONS</b>	Short-time delayed tripping
<b>SENSITIVITY TYPE</b>	Pulse-current sensitive
<b>RADIATION RESISTANCE</b>	Suitable for variable frequency drives (enhanced sensitivity)
<b>TERMINAL CAPACITY (CABLE)</b>	M5 (with cross-recessed screw as defined in EN ISO 4757-Z2, PZ2)
<b>RATED FAULT CURRENT - MAX</b>	0.03 A
<b>RATED FAULT CURRENT - MIN</b>	0.03 A
<b>RATED INSULATION VOLTAGE (UI)</b>	440 V
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	100 A
<b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>	415 V
<b>RATED RESIDUAL MAKING AND BREAKING CAPACITY</b>	1000 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>	0 W

SURGE CURRENT CAPACITY	3 kA
WIDTH IN NUMBER OF MODULAR SPACINGS	4
VOLTAGE RATING (IEC/EN 60947-2)	240 V AC / 415 V AC
TERMINAL CAPACITY (SOLID WIRE)	1.5 mm <sup>2</sup> - 35 mm <sup>2</sup>
TRIPPING TIME	Short time-delayed 10 ms delayed
RATED SHORT-CIRCUIT STRENGTH	10 kA with back-up fuse
TIGHTENING TORQUE	2 Nm - 2.4 Nm
TERMINAL CAPACITY (STRANDED CABLE)	16 mm <sup>2</sup> (2x)
