

## Eaton 170585

Eaton Moeller series xEffect - FRBm6/M RCBO - residual-current circuit breaker with overcurrent protection. RCD/MCB, 32A, 300mA, MCB trip type C, 1-ph+N, RCCB trip type: AC, G

|                             |                                                                                                            |
|-----------------------------|------------------------------------------------------------------------------------------------------------|
|                             |                                                                                                            |
| <b>PRODUCT NAME</b>         | Eaton Moeller series xEffect - FRBm6/M RCBO - residual-current circuit breaker with overcurrent protection |
| <b>CATALOG NUMBER</b>       | 170585                                                                                                     |
| <b>PRODUCT LENGTH/DEPTH</b> | 80 mm                                                                                                      |
| <b>PRODUCT HEIGHT</b>       | 75 mm                                                                                                      |
| <b>PRODUCT WIDTH</b>        | 35 mm                                                                                                      |
| <b>PRODUCT WEIGHT</b>       | 0.206 kg                                                                                                   |
| <b>COMPLIANCES</b>          | CE Marked<br>RoHS conform                                                                                  |
| <b>CERTIFICATIONS</b>       | CE<br>EN45545-2<br>IEC 61373                                                                               |

|                                                                                         |                                                                                                                                  |
|-----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| <b>VOLTAGE RATING</b>                                                                   | 240 V - 240 V                                                                                                                    |
| <b>SURGE CURRENT CAPACITY</b>                                                           | 3 kA                                                                                                                             |
| <b>VOLTAGE TYPE</b>                                                                     | AC                                                                                                                               |
| <b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>                                              | 2                                                                                                                                |
| <b>FEATURES</b>                                                                         | Concurrently switching N-neutral<br>Anti- nuisance tripping version                                                              |
| <b>10.10 TEMPERATURE RISE</b>                                                           | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| <b>10.11 SHORT-CIRCUIT RATING</b>                                                       | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>                                              | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.13 MECHANICAL FUNCTION</b>                                                        | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| <b>10.2.2 CORROSION RESISTANCE</b>                                                      | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>                         | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>       | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b> | Meets the product standard's requirements.                                                                                       |
| <b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>                                 | Meets the product standard's requirements.                                                                                       |
| <b>10.2.5 LIFTING</b>                                                                   | Does not apply, since the                                                                                                        |

|                                                                       |
|-----------------------------------------------------------------------|
| <a href="#">xEffect FR RCCB FAZ%20MCB.pdf</a>                         |
| <a href="#">eaton-xeffect-frbm6-rcbo-catalog-ca003015en-en-us.pdf</a> |
| <a href="#">eaton-xeffect-frbm6m-dimensions.jpg</a>                   |
| <a href="#">eaton-xeffect-frbm6m-wiring-diagram.jpg</a>               |
| <a href="#">eaton-xeffect-frbm6m-characteristic-curve.jpg</a>         |
| <a href="#">eaton-xeffect-frbm6m-3d-drawing-006.jpg</a>               |

|                                                                      |                                                                    |
|----------------------------------------------------------------------|--------------------------------------------------------------------|
|                                                                      | entire switchgear needs to be evaluated.                           |
| <b>10.2.6 MECHANICAL IMPACT</b>                                      | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.2.7 INSCRIPTIONS</b>                                           | Meets the product standard's requirements.                         |
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                       | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                        | Meets the product standard's requirements.                         |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                        | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>        | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>             | Is the panel builder's responsibility.                             |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                      | Is the panel builder's responsibility.                             |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                      | Is the panel builder's responsibility.                             |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                              | Is the panel builder's responsibility.                             |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>      | Is the panel builder's responsibility.                             |
| <b>OPERATING AMBIENT TEMPERATURE - MAX</b>                           | 40 °C                                                              |
| <b>OPERATING AMBIENT TEMPERATURE - MIN</b>                           | -25 °C                                                             |
| <b>PRODUCT RANGE</b>                                                 | FRBmM                                                              |
| <b>RATED CURRENT</b>                                                 | 32 A                                                               |
| <b>RATED FAULT CURRENTS OF PRODUCT RANGE</b>                         | 10, 30, 100, 300 MilliAmpere                                       |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b> | 32 A                                                               |
| <b>RATED SWITCHING CAPACITY (IEC/EN 61009)</b>                       | 10 kA                                                              |
| <b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT</b>                | 0 W                                                                |
| <b>TRIPPING</b>                                                      | C                                                                  |

|                                                            |                                                             |
|------------------------------------------------------------|-------------------------------------------------------------|
| <b>CHARACTERISTIC</b>                                      |                                                             |
| <b>BUILT-IN DEPTH</b>                                      | 75.5 mm                                                     |
| <b>CURRENT LIMITING CLASS</b>                              | 3                                                           |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60947-2)</b>  | 10 kA                                                       |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                 | 40 °C                                                       |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                 | -25 °C                                                      |
| <b>FAULT CURRENT RATING</b>                                | 0.3 A                                                       |
| <b>HEAT DISSIPATION CAPACITY</b>                           | 0 W                                                         |
| <b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>        | 0 W                                                         |
| <b>NUMBER OF POLES (PROTECTED)</b>                         | 1                                                           |
| <b>NUMBER OF POLES (TOTAL)</b>                             | 2                                                           |
| <b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>                | 240 V                                                       |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY (IEC 60947-2)</b> | 10 kA                                                       |
| <b>RATED SWITCHING CAPACITY</b>                            | 10 kA                                                       |
| <b>BASIC FUNCTION</b>                                      | Combined RCD/MCB devices                                    |
| <b>MOUNTING METHOD</b>                                     | DIN rail                                                    |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>       | 6.1 W                                                       |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>              | 4 kV                                                        |
| <b>DEGREE OF PROTECTION</b>                                | IP20                                                        |
| <b>OPERATING AMBIENT TEMPERATURE HINT</b>                  | Keep in mind the derating at temperatures higher than 40 °C |
| <b>TRIPPING</b>                                            | Short time-delayed                                          |
| <b>OVERVOLTAGE CATEGORY</b>                                | III                                                         |
| <b>POLLUTION DEGREE</b>                                    | 2                                                           |
| <b>IMPULSE WITHSTAND CURRENT</b>                           | Surge-proof, 3 kA                                           |

|                                                                |                                                                |
|----------------------------------------------------------------|----------------------------------------------------------------|
| <b>LEAKAGE CURRENT TYPE</b>                                    | AC                                                             |
| <b>RELEASE CHARACTERISTIC</b>                                  | C                                                              |
| <b>SENSITIVITY TYPE</b>                                        | AC current sensitive                                           |
| <b>FREQUENCY RATING</b>                                        | 50 Hz                                                          |
| <b>RATED INSULATION VOLTAGE (UI)</b>                           | 500 V                                                          |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>  | 1 mm <sup>2</sup>                                              |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>  | 25 mm <sup>2</sup>                                             |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b> | 1 mm <sup>2</sup>                                              |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b> | 25 mm <sup>2</sup>                                             |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 61009)</b>        | 10 kA                                                          |
| <b>RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 61009-1)</b>      | 10 kA                                                          |
| <b>NUMBER OF POLES</b>                                         | Single-pole + N                                                |
| <b>DISCONNECTION CHARACTERISTIC</b>                            | Short-time delayed                                             |
| <b>TYPE</b>                                                    | RCBO                                                           |
| <b>APPLICATION</b>                                             | Switchgear for industrial and advanced commercial applications |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

