


Eaton 170E3844

Fuse-link, high speed, 63 A, DC 900 V, DIN 00, aR, DIN, IEC, with indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170E3844
UPC	051712209311
PRODUCT LENGTH/DEPTH	233 mm
PRODUCT HEIGHT	66 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	244.5 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	63 A
BREAKING CAPACITY	300 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	900 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
WATT LOSSES	21 W
FUSE SHAPE	Square body, slotted offset bolted tags
COLOR	None
INTERRUPT RATING	300 kAIC
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	900 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag DIN 43653
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

