



## Eaton 170M0213

Fuse-link, high speed, 40 A, AC 660 V, size 0000, 18 x 19 x 80 mm, gR, UL

### □□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M0213
<b>UPC</b>	051712216296
<b>PRODUCT LENGTH/DEPTH</b>	140 mm
<b>PRODUCT HEIGHT</b>	40 mm
<b>PRODUCT WIDTH</b>	102 mm
<b>PRODUCT WEIGHT</b>	48.2 g
<b>COMPLIANCES</b>	Contact factory RoHS Compliant



*Powering Business Worldwide*

□□□□	
AMPERAGE RATING	40 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	0000
RATED VOLTAGE AC	660 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	63.3 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M6
CLASS	Class gR
WATT LOSSES	11 W
FUSE SHAPE	Square body, offset bolted tags
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	0000
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:

□□	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf</a>



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

