

Eaton 170M0216

Fuse-link, high speed, 80 A, AC 660 V, size 0000, 18 x 19 x 80 mm, aR, UL

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M0216
UPC	051712216326
PRODUCT LENGTH/DEPTH	140 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	102 mm
PRODUCT WEIGHT	48.2 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	80 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	0000
RATED VOLTAGE AC	660 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	63.3 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M6
CLASS	Class aR
WATT LOSSES	17 W
FUSE SHAPE	Square body, offset bolted tags
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	0000
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

