

Eaton 170M1572D

Fuse-link, high speed, 315 A, AC 690 V, 200 kA, DIN 00, aR, DIN, IEC, type T indicator, square body with knife blade contacts

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M1572D
UPC	051712334938
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	69 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	204 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	315 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	690 V
CURRENT TYPE	AC
CLASS	Class aR
CLEARING (I2T)	84500 at 660 V
WATT LOSSES	45 W
FUSE SHAPE	Square body, knife blade contacts
PRE ARC (I2T)	12000
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Dual indicator
CONNECTION	Din 43-620 blade end x Din 43-620 blade end
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43620 Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

