



Eaton 170965

Eaton Moeller series xEffect - FRBm4 RCBO - residual-current circuit breaker with overcurrent protection. RCD/MCB, 20A, 300mA, MCB trip type D, 3-ph+N, RCCB trip type: AC

□□□□

PRODUCT NAME	Eaton Moeller series xEffect - FRBm4 RCBO - residual-current circuit breaker with overcurrent protection
CATALOG NUMBER	170965
PRODUCT LENGTH/DEPTH	80 mm
PRODUCT HEIGHT	75.5 mm
PRODUCT WIDTH	70 mm
PRODUCT WEIGHT	0.461 kg
COMPLIANCES	CE Marked RoHS conform
CERTIFICATIONS	CE EN45545-2 IEC 61373

□□□□

VOLTAGE RATING	415 V - 415 V
SURGE CURRENT CAPACITY	0.25 kA
VOLTAGE TYPE	AC
WIDTH IN NUMBER OF MODULAR SPACINGS	4
FEATURES	Concurrently switching N-neutral
OPERATING AMBIENT TEMPERATURE - MAX	40 °C
OPERATING AMBIENT TEMPERATURE - MIN	-25 °C
PRODUCT RANGE	FRBm4
RATED CURRENT	20 A
RATED FAULT CURRENTS OF PRODUCT RANGE	30, 100, 300 MilliAmpere
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	20 A
RATED SWITCHING CAPACITY (IEC/EN 61009)	4.5 kA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
TRIPPING CHARACTERISTIC	D
BUILT-IN DEPTH	75.5 mm
CURRENT LIMITING CLASS	3
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 60947-2)	0 kA
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
FAULT CURRENT RATING	0.3 A
HEAT DISSIPATION CAPACITY	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT	0 W
NUMBER OF POLES (PROTECTED)	4
NUMBER OF POLES (TOTAL)	4
RATED OPERATIONAL VOLTAGE (UE) - MAX	415 V

□□

□□□□	eaton-xeffect-frbm4-rcbo-catalog-ca003016en-en-us.pdf
□□	eaton-xeffect-frbm6m-characteristic-curve-002.jpg
	eaton-xeffect-frbm6m-dimensions-004.jpg
	eaton-xeffect-frbm6m-wiring-diagram-002.jpg

RATED SWITCHING CAPACITY	4.5 kA
BASIC FUNCTION	Combined RCD/MCB devices
MOUNTING METHOD	DIN rail
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	12 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4 kV
DEGREE OF PROTECTION	IP20
OPERATING AMBIENT TEMPERATURE HINT	Keep in mind the derating at temperatures higher than 40 °C
TRIPPING	Non-delayed
OVERVOLTAGE CATEGORY	III
POLLUTION DEGREE	2
IMPULSE WITHSTAND CURRENT	Partly surge-proof, 250 A
LEAKAGE CURRENT TYPE	AC
RELEASE CHARACTERISTIC	D
SENSITIVITY TYPE	AC current sensitive
FREQUENCY RATING	50 Hz
RATED INSULATION VOLTAGE (UI)	500 V
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX	25 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN	1 mm ²
CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX	25 mm ²
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 61009)	4.5 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY (EN 61009-1)	4.5 kA
NUMBER OF POLES	Three-pole + N

DISCONNECTION CHARACTERISTIC	Undelayed
TYPE	RCBO
APPLICATION	Switchgear for industrial and advanced commercial applications
