

Eaton 170M2052

Fuse-link, high speed, 80 A, DC 2000 V, 39 x 66 x 216 mm, aR, IEC, with indicator

PRODUCT NAME	Eaton Bussmann series high speed traction fuse
CATALOG NUMBER	170M2052
UPC	051712486910
PRODUCT LENGTH/DEPTH	216 mm
PRODUCT HEIGHT	66 mm
PRODUCT WIDTH	39 mm
PRODUCT WEIGHT	461.2 g
COMPLIANCES	Not Applicable RoHS Compliant
CERTIFICATIONS	IEC Rated

USED WITH	Protection of DC third rail applications up to 2000 Vdc
AMPERAGE RATING	80 A
BREAKING CAPACITY	100 kA
VOLTAGE TYPE	DC
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
FUSE INDICATOR	Other
CLASS	Class aR
CLEARING (I2T)	4550
WATT LOSSES	53 W
FUSE SHAPE	Square body, offset bolted tags
PRE ARC (I2T)	1555
RATED VOLTAGE DC	2000 V
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	2000 V
TYPE	Fuse
APPLICATION	<ul style="list-style-type: none"> • traction • third rail
FITTED WITH:	Single slot tags
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: