

Eaton 170M2659

Eaton Bussmann series high speed square body fuse, 700V (UL), 690V (IEC), 32A, 200 kAIC, Top fuse status indicator, Fuse, Blade end X blade end, Class gR, DIN 43 620

| | |
|-----------------------------|---|
| | |
| PRODUCT NAME | Eaton Bussmann series high speed square body fuse |
| CATALOG NUMBER | 170M2659 |
| UPC | 051712792134 |
| PRODUCT LENGTH/DEPTH | 233 mm |
| PRODUCT HEIGHT | 66 mm |
| PRODUCT WIDTH | 140 mm |
| PRODUCT WEIGHT | 235.3333333 g |
| COMPLIANCES | CE Marked RoHS Compliant |
| CERTIFICATIONS | IEC Rated UL Recognized |

| | |
|---|--|
| | |
| AMPERAGE RATING | 32 A |
| BREAKING CAPACITY | 200 kA |
| FUSE INDICATOR | Top fuse status indicator |
| INSULATED METAL GRIPPING LUGS (IMGL) | No |
| UTILIZATION CATEGORY | gR (general purpose semiconductor protection) |
| VOLTAGE TYPE | AC |
| FUSE SIZE | 00 |
| RATED VOLTAGE AC | 690 V |
| CENTER-TO-CENTER DISTANCE OF CONNECTIONS | 78 mm |
| CURRENT TYPE | AC |
| MOUNTING DIMENSION | M10 |
| CLASS | Class gR |
| CLEARING (I2T) | 195 at 660 V |
| WATT LOSSES | 7 W |
| FUSE SHAPE | Square body, slotted offset bolted tags |
| PRE ARC (I2T) | 28.5 |
| COLOR | None |
| INTERRUPT RATING | 200 kAIC |
| CONNECTION | Blade end x blade end |
| CONSTRUCTION SIZE | 00 |
| MOUNTING METHOD | DIN 43 620 |
| PACKAGING TYPE | Standard |
| VOLTAGE RATING | 690 V (IEC) |
| TYPE | Fuse |
| APPLICATION | Semiconductor, DC Common bus, DC drives, power converters/rectifiers |
| FUSE TYPE | DIN 43653 /80 Visual indicator |
| FUSE SYSTEM (ACCORDING TO IEC 60269) | Other |

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250982en.pdf](#)

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

