

Eaton 170M1311

Fuse-link, high speed, 25 A, AC 690 V, DIN 000, 21 x 40 x 100 mm, gR, DIN, IEC

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M1311
UPC	051712216470
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	0.13 kg
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	25 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	000
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	76.7 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class gR
CLEARING (I2T)	130 at 660 V
WATT LOSSES	9 W
FUSE SHAPE	Square body, slotted offset bolted tags
PRE ARC (I2T)	19
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	000
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 U/80 Without indicator Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

