



Eaton 170M2758

Eaton Bussmann series high speed square body fuse, fuse-link, high speed, 25 A, AC 690 V, size 00, 30 x 62 x 64 mm, gR, IEC, single indicator



PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M2758
UPC	051712254397
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	77 mm
PRODUCT WIDTH	163 mm
PRODUCT WEIGHT	211 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



Powering Business Worldwide



AMPERAGE RATING	25 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	64 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class gR
CLEARING (I2T)	130 at 660 V
WATT LOSSES	6 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I2T)	19
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	00
MOUNTING METHOD	DIN 43 620 Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end 00BTN/60 Type T indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A



DECLARATIONS OF
CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

