

Eaton 170M1359

Fuse-link, high speed, 16 A, AC 690 V, DIN 000, 21 x 40 x 100 mm, gR, DIN, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M1359
UPC	051712216609
PRODUCT LENGTH/DEPTH	21 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	100 mm
PRODUCT WEIGHT	144.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	16 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	000
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	76.7 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class gR
CLEARING (I₂T)	48 at 660 V
WATT LOSSES	5.5 W
FUSE SHAPE	Square body, slotted offset bolted tags
PRE ARC (I₂T)	7.2
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	000
MOUNTING METHOD	DIN 43 620
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag DIN 43653
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

[eaton-fuses-fuse-link-dimensions-005.eps](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

