

Eaton 170M1412

Fuse-link, high speed, 32 A, AC 690 V, DIN 000, gR, DIN, IEC, single indicator, live gripping lugs

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M1412
UPC	051712216784
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	53 mm
PRODUCT WIDTH	21 mm
PRODUCT WEIGHT	145.8 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	32 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	000
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class gR
CLEARING (I2T)	270 at 660 V
WATT LOSSES	10 W
FUSE SHAPE	Square body, slotted offset bolted tags
PRE ARC (I2T)	40
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	000
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 TN/80 Type T Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

