



## Eaton 170M2611

Eaton Bussmann series high speed square body fuse, 700V (UL), 690V (IEC), 50A, 200 kAIC, Top fuse status indicator, Fuse, Blade end X blade end, Class gR, DIN 43 620

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M2611
<b>UPC</b>	051712254106
<b>PRODUCT LENGTH/DEPTH</b>	233 mm
<b>PRODUCT HEIGHT</b>	66 mm
<b>PRODUCT WIDTH</b>	140 mm
<b>PRODUCT WEIGHT</b>	216 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC Rated UL Recognized

□□□□	
AMPERAGE RATING	50 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class gR
CLEARING (I2T)	640 at 660 V
WATT LOSSES	10 W
FUSE SHAPE	Square body, slotted offset bolted tags
PRE ARC (I2T)	95
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 /80 Visual indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250982en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

