



Eaton 170M3148

Eaton Bussmann series high speed square body fuse,400A,100 kAIC,Class aR,,DIN 43 620,Standard,Clearing at 1000V: 265000 , Clearing at 1250V: 335000,square body with centre-bolted tags (slotted),Top fuse status indicator,53000,70W

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3148
UPC	051712255035
PRODUCT LENGTH/DEPTH	305 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	145 mm
PRODUCT WEIGHT	425 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



Powering Business Worldwide

□□□□

AMPERAGE RATING	400 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	1250 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	107 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I₂T)	265000 at 1000 V, 335000 at 1250 V
WATT LOSSES	70 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I₂T)	53000
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	1250 V (IEC), 1300 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 /110 Visual indicator Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250914en.pdf](#)

