

Eaton 170M2692

Eaton Bussmann series high speed square body fuse, 700V (UL), 690V (IEC), 16A, 200 kAIC, Top fuse status indicator, Fuse, Blade end X Din 43-620 blade end, Class gR, DIN 43 620

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M2692
UPC	051712540261
PRODUCT LENGTH/DEPTH	217 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	85 mm
PRODUCT WEIGHT	218 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	16 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	690 V
CURRENT TYPE	AC
CLASS	Class gR
CLEARING (I2T)	38 at 600 V
WATT LOSSES	5.5 W
FUSE SHAPE	Square body, knife blade contacts
PRE ARC (I2T)	7.2
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
CONNECTION	Blade end x Din 43-620 blade end
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43620 T indicator for micro Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

