

Eaton 170M3268

Fuse-link, high speed, 350 A, AC 690 V,
compact DIN 1, 45 x 58 x 134 mm, aR, DIN,
IEC, type K indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3268
UPC	051712799805
PRODUCT LENGTH/DEPTH	305 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	145 mm
PRODUCT WEIGHT	340.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	350 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	106 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	68500 at 660 V
WATT LOSSES	55 W
CLEARING LOSS	55
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	10000
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	DIN 43 620
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag DIN 43653
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

