

Eaton 170M3389

Fuse-link, high speed, 63 A, AC 1250 V,
compact size 1, 45 x 59 x 75 mm, aR, IEC, UL,
single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3389
UPC	051712255868
PRODUCT LENGTH/DEPTH	160 mm
PRODUCT HEIGHT	60 mm
PRODUCT WIDTH	92 mm
PRODUCT WEIGHT	351 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	63 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	1*
RATED VOLTAGE AC	1250 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	74 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class aR
CLEARING (I2T)	1300 at 1000 V, 1750 at 1250 V
WATT LOSSES	20 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I2T)	215
COLOR	None
INTERRUPT RATING	100 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	1250 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/75 Type K Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

