



Eaton 170M2761

Eaton Bussmann series high speed square body fuse, fuse-link, high speed, 50 A, AC 690 V, size 00, 30 x 62 x 64 mm, gR, IEC, single indicator



PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M2761
UPC	051712254427
PRODUCT LENGTH/DEPTH	64 mm
PRODUCT HEIGHT	62 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.001 g
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC Rated



Powering Business Worldwide



AMPERAGE RATING	50 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	64 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class gR
CLEARING (I2T)	640 at 660 V
WATT LOSSES	10 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I2T)	95
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
CONSTRUCTION SIZE	00
MOUNTING METHOD	Single Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC)
TYPE	Fuse
SPECIAL FEATURES	Indicator style T for microswitch, Electric engineering
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end 00BTN/60 Type T indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A



DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

