



□□□□□

## Eaton 170M4310

Fuse-link, high speed, 315 A, AC 690 V, size 1, 53 x 69 x 111 mm, aR, IEC, single indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M4310
<b>UPC</b>	051712258401
<b>PRODUCT LENGTH/DEPTH</b>	62 mm
<b>PRODUCT HEIGHT</b>	142 mm
<b>PRODUCT WIDTH</b>	230 mm
<b>PRODUCT WEIGHT</b>	0.001 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC Rated UL Recognized

## □□□□

AMPERAGE RATING	315 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	86.5 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	42000 at 660 V
WATT LOSSES	58 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	6200
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
CONSTRUCTION SIZE	1
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	French style E/Type indicator for micro Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

## □□

### DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250910en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

