



## Eaton 170M3261

Fuse-link, high speed, 80 A, AC 690 V,  
compact DIN 1, 45 x 58 x 134 mm, aR, DIN,  
IEC, single indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M3261
<b>UPC</b>	051712255455
<b>PRODUCT LENGTH/DEPTH</b>	305 mm
<b>PRODUCT HEIGHT</b>	65 mm
<b>PRODUCT WIDTH</b>	145 mm
<b>PRODUCT WEIGHT</b>	346 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	UL Recognized IEC Rated

□□□□

AMPERAGE RATING	80 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	106 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I <sub>2</sub> T)	1250 at 660 V
WATT LOSSES	18 W
CLEARING LOSS	18
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I <sub>2</sub> T)	185
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
MOUNTING METHOD	DIN 43 620
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag DIN 43653
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF  
CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250915en.pdf](#)

---

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

