



□□□□

## Eaton 170M4709

Fuse-link, high speed, 250 A, AC 690 V, size 1,  
53 x 69 x 136 mm, aR, IEC, UL

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M4709
<b>UPC</b>	051712259590
<b>PRODUCT LENGTH/DEPTH</b>	58 mm
<b>PRODUCT HEIGHT</b>	54 mm
<b>PRODUCT WIDTH</b>	170 mm
<b>PRODUCT WEIGHT</b>	487 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC Rated UL Recognized



Powering Business Worldwide



<b>AMPERAGE RATING</b>	250 A
<b>BREAKING CAPACITY</b>	200 kA
<b>FUSE INDICATOR</b>	None
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC
<b>FUSE SIZE</b>	1
<b>RATED VOLTAGE AC</b>	690 V
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	114 mm
<b>CURRENT TYPE</b>	AC
<b>MOUNTING DIMENSION</b>	M12
<b>CLASS</b>	Class aR
<b>CLEARING (I2T)</b>	21000 at 660 V
<b>WATT LOSSES</b>	55 W
<b>FUSE SHAPE</b>	Square body, center bolted tags
<b>PRE ARC (I2T)</b>	3100
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONNECTION</b>	Blade end x blade end
<b>CONSTRUCTION SIZE</b>	1
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	690 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
<b>FUSE TYPE</b>	US Style FU/115 without indicator Bolted tag
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other



DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250911en.pdf](#)

