



## Eaton 170M3464

Fuse-link, high speed, 160 A, AC 690 V,  
compact size 1, aR, IEC, UL, single indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M3464
<b>UPC</b>	051712799966
<b>PRODUCT LENGTH/DEPTH</b>	60 mm
<b>PRODUCT HEIGHT</b>	50 mm
<b>PRODUCT WIDTH</b>	43 mm
<b>PRODUCT WEIGHT</b>	44.2 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC Rated UL Recognized

□□□□

AMPERAGE RATING	160 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	50 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class aR
CLEARING (I <sub>2</sub> T)	7500 at 660 V
WATT LOSSES	30 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I <sub>2</sub> T)	1100
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/Type K Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250915en.pdf](#)

