

Eaton 170M3619

Eaton Bussmann series high speed square body fuse, 700V (UL), 690V (IEC), 400A, 200 kAIC, None, Fuse, Blade end X blade end, Class aR

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3619
UPC	051712799096
PRODUCT LENGTH/DEPTH	305 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	145 mm
PRODUCT WEIGHT	319 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	400 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78.5 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	105000 at 660 V
WATT LOSSES	60 W
FUSE SHAPE	Square body, center bolted tags
PRE ARC (I2T)	15000
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	US Style FU/Without indicator Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

