

Eaton 170M4834

Fuse-link, high speed, 250 A, AC 1000 V, size 00, 30 x 47 x 98 mm, aR, DIN, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M4834
UPC	051712798518
PRODUCT LENGTH/DEPTH	233 mm
PRODUCT HEIGHT	66 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	248 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	250 A
BREAKING CAPACITY	125 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	74000 at 1000 V
WATT LOSSES	48 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	10000
COLOR	None
INTERRUPT RATING	125 kAIC
CONNECTION	Blade end x Din 43-620 blade end
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 00TN/80 Type T Indicator for micro Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

