

# Eaton 170M5391

Fuse-link, high speed, 350 A, AC 1250 V, size 2, 61 x 75 x 77 mm, aR, IEC, UL, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5391
UPC	051712261067
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	124 mm
PRODUCT WEIGHT	743.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	350 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	1250 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	74.3 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	97500 at 1000 V, 135000 at 1250 V
WATT LOSSES	80 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I2T)	16500
COLOR	None
INTERRUPT RATING	100 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	2
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	1250 V (IEC), 1300 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/75 Type K Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

