



Eaton 170M5408

Eaton Bussmann series high speed square body fuse, 690 V (IEC), 700 V (UL), 400 A, Fuse size: 2, Top fuse status indicator, Flush end, B/Visual indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5408
UPC	051712261135
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	124 mm
PRODUCT WEIGHT	308.5 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

□□□□

AMPERAGE RATING	400 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	50.4 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I ₂ T)	74000 at 660 V
WATT LOSSES	65 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I ₂ T)	11000
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	2
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end B/Visual indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251012en.pdf
----------------------------	--

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

