

Eaton 170M5806

Fuse-link, high speed, 315 A, AC 690 V,
compact DIN 2, 55 x 71 x 150 mm, aR, DIN,
IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5806
UPC	051712798587
PRODUCT LENGTH/DEPTH	210 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	160 mm
PRODUCT WEIGHT	661 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	315 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	02
RATED VOLTAGE AC	690 V
CURRENT TYPE	AC
CLASS	Class aR
WATT LOSSES	61 W
FUSE SHAPE	Square body, knife blade contacts
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	DIN 43620 Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: