



□□□□□

Eaton 170M5974

Fuse-link, high speed, 700 A, AC 1000 V, DIN 2, 59 x 77 x 138 mm, aR, DIN, IEC, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5974
UPC	051712602365
PRODUCT LENGTH/DEPTH	284 mm
PRODUCT HEIGHT	67 mm
PRODUCT WIDTH	175 mm
PRODUCT WEIGHT	872 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

□□□□

AMPERAGE RATING	700 A
BREAKING CAPACITY	125 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	108 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I ₂ T)	770000 at 1000 V
WATT LOSSES	115 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I ₂ T)	130000
COLOR	None
INTERRUPT RATING	125 kAIC
CONSTRUCTION SIZE	2
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 KN/110 Type K Indicator for Micro Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250974en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

