



□□□□□

Eaton 170M5058

Fuse-link, high speed, 400 A, AC 690 V, DIN 2, 61 x 75 x 108 mm, aR, DIN, IEC, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5058
UPC	051712259941
PRODUCT LENGTH/DEPTH	286 mm
PRODUCT HEIGHT	66 mm
PRODUCT WIDTH	165 mm
PRODUCT WEIGHT	594 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

TNT	
AMPERAGE RATING	400 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	74000 at 660 V
WATT LOSSES	65 W
CLEARING LOSS	65
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	1100
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	2
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 TN/80 Type T Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

