

Eaton 170M6171

Eaton Bussmann series high speed square body fuse, 550 V AC, 2000 A, Fuse size: 3, Top fuse status indicator, DIN 43653, /110 Visual indicator, Bolted tag

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6171
UPC	051712263177
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	1230 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	2000 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	550 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	108 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	6350000 at 660 V
WATT LOSSES	175 W
CLEARING LOSS	175
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	1150000
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	550 V AC
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 /110 Visual indicator Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250905en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

