



Eaton 170M6697

Fuse-link, high speed, 900 A, AC 1250 V, size 3, 76 x 92 x 159 mm, aR, IEC, UL

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6697
UPC	051712265195
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	1.527 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated CSA Certified

□□□□

AMPERAGE RATING	900 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	1250 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	114 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CLASS	Class aR
CLEARING (I ₂ T)	1500000 at 1000 V, 1900000 at 1250 V
WATT LOSSES	130 W
FUSE SHAPE	Square body, center bolted tags
PRE ARC (I ₂ T)	305000
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	1250 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	US Style FU/115 without indicator Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250907en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

