

Eaton 170M6812D

Eaton Bussmann series high speed square body fuse, 690V, 800A, 200 kAIC, Combination fuse status indicator, Fuse, Din 43-620 blade end X Din 43-620 blade end, Class aR

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6812D
UPC	051712335256
PRODUCT LENGTH/DEPTH	150 mm
PRODUCT HEIGHT	87 mm
PRODUCT WIDTH	71 mm
PRODUCT WEIGHT	1114 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	800 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Combination fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	690 V
CURRENT TYPE	AC
CLASS	Class aR
CLEARING (I2T)	490000 at 660 V
WATT LOSSES	48 W
FUSE SHAPE	Square body, knife blade contacts
PRE ARC (I2T)	69500
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Dual indicator
CONNECTION	Din 43-620 blade end x Din 43-620 blade end
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43620 Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

