



Eaton 170M6881

Eaton Bussmann series high speed square body fuse, 1400 A, AC 660 V, 2 x size 3, 74 x 167 x 52 mm, aR, IEC, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6881
UPC	051712265812
PRODUCT LENGTH/DEPTH	167 mm
PRODUCT HEIGHT	52 mm
PRODUCT WIDTH	90 mm
PRODUCT WEIGHT	0.001 g
COMPLIANCES	CE RoHS Compliant EAC
CERTIFICATIONS	IEC 60269-4



Powering Business Worldwide



AMPERAGE RATING	1400 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Top fuse status indicator
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	23
RATED VOLTAGE AC	660 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	52 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	1350000 at 660 V
WATT LOSSES	210 W
FUSE SHAPE	Square body flush end contacts
PRE ARC (I2T)	200000
COLOR	None
INTERRUPT RATING	100 kAIC
CONNECTION	Flush-end contact
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/55 Type K indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

