



□□□□□

Eaton 170M8511

Fuse-link, high speed, 1100 A, AC 1000 V, size 3, 74 x 92 x 91 mm, aR, IEC, UL, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M8511
UPC	051712603867
PRODUCT LENGTH/DEPTH	90 mm
PRODUCT HEIGHT	74 mm
PRODUCT WIDTH	160 mm
PRODUCT WEIGHT	2550 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

□□□□

AMPERAGE RATING	1100 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	75.4 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I ₂ T)	2750000 at 1000 V
WATT LOSSES	155 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I ₂ T)	460000
COLOR	None
INTERRUPT RATING	100 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	3
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end GKN/Type K indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250908en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

