

Eaton 170M6118

Fuse-link, high speed, 1500 A, AC 690 V, DIN 3, 76 x 92 x 109 mm, aR, DIN, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6118
UPC	051712262880
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	940 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	1500 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	78 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	3100000 at 660 V
WATT LOSSES	160 W
CLEARING LOSS	160
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	460000
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 KN/80 Type K Indicator for Micro Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

