



□□□□□

## Eaton 171329

Eaton Moeller® series SL4 Continuous light module, yellow, LED, 230 V

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series SL4 Continuous light module
<b>CATALOG NUMBER</b>	171329
<b>PRODUCT LENGTH/DEPTH</b>	43 mm
<b>PRODUCT HEIGHT</b>	75 mm
<b>PRODUCT WIDTH</b>	43 mm
<b>PRODUCT WEIGHT</b>	0.043 kg
<b>CERTIFICATIONS</b>	CSA-C22.2 No. 94-91 UL 508 UL CSA-C22.2 No. 14-10 CE CSA Class No.: NKCR7 UL File No.: E29184 UL Category Control No.: NKCR IEC/EN 60947-5-1 UL report applies to both US and Canada IEC/EN 60529 Certified by UL for use in Canada

## □□□□

<b>TYPE</b>	Continuous light module
<b>PRODUCT CATEGORY</b>	SL signal towers
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	4000 V AC
<b>ENCLOSURE COLOR</b>	Black
<b>FUNCTIONS</b>	Continuous light
<b>COLOR</b>	Yellow
<b>VOLTAGE TYPE</b>	AC
<b>MATERIAL</b>	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
<b>MOUNTING POSITION</b>	As required
<b>DEGREE OF PROTECTION</b>	NEMA 4X IP66
<b>LAMP TYPE</b>	LED
<b>OVERVOLTAGE CATEGORY</b>	III
<b>CURRENT CONSUMPTION</b>	34 mA at 230/240 V AC
<b>LIFESPAN, ELECTRICAL</b>	100,000 h
<b>LIGHT TYPE</b>	Continuous light
<b>LIGHT MODULES</b>	LED
<b>NUMBER OF MODULES</b>	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
<b>SHOCK RESISTANCE</b>	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	240 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN</b>	230 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT DC -</b>	0 V

## □□

DECLARATIONS OF CONFORMITY	<a href="#">eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf</a>
□□□□□	<a href="#">IL047001ZU</a>
	<a href="#">eaton-operating-sl4-continuous-light-dimensions.eps</a>
□□	<a href="#">eaton-operating-sl7-continuous-light-symbol-002.eps</a>
	<a href="#">eaton-operating-button-sl7-continuous-light-symbol-004.eps</a>

MAX	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	43 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V
