



Eaton 170M6501

Fuse-link, high speed, 1400 A, AC 1100 V, size 3, 76 x 92 x 83 mm, aR, IEC, UL, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6501
UPC	051712264310
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	1356 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

□□□□

AMPERAGE RATING	1400 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	3
RATED VOLTAGE AC	1100 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	91.4 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M12
CLASS	Class aR
CLEARING (I₂T)	6000000 at 1000 V
WATT LOSSES	150 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I₂T)	1250000
COLOR	None
INTERRUPT RATING	100 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	3
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	1100 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/90 Type K Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

