

Eaton 171341

Eaton Moeller® series SL4 Flashing light module, yellow, LED, 24 V

PRODUCT NAME	Eaton Moeller® series SL4 Flashing light module
CATALOG NUMBER	171341
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.042 kg
CERTIFICATIONS	Certified by UL for use in Canada IEC/EN 60947-5-1 UL 508 CSA-C22.2 No. 14-10 CE CSA-C22.2 No. 94-91 UL Category Control No.: NKCR IEC/EN 60529 UL File No.: E29184 CSA Class No.: NKCR7 UL UL report applies to both US and Canada

TYPE	Flashing light module
PRODUCT CATEGORY	SL signal towers
POLLUTION DEGREE	3
FLASHING FREQUENCY	2 Hz
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Blinker light
COLOR	Yellow
VOLTAGE TYPE	AC/DC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 4 IP66
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	50 mA at 24 V AC/DC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Flashing light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 10 (with base for mounting on both sides) Max. 5 (with standard base)
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	24 V
RATED OPERATIONAL	24 V

DECLARATIONS OF CONFORMITY	eaton-continuous-light-module-declaration-of-conformity-uk251039en.pdf
	IL047001ZU
	eaton-operating-sl4-continuous-light-dimensions.eps
	eaton-operating-button-sl7-continuous-light-symbol-004.eps
	eaton-operating-sl7-flashing-light-symbol.eps

VOLTAGE (UE) AT AC - MIN	
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	24 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	24 V
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-30 °C
LEAKAGE CURRENT	0.003 A
OUTSIDE DIAMETER	43 mm
RADIATION ANGLE	360 °
RATED INSULATION VOLTAGE (UI)	250 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

