

# Eaton 171376

Eaton Moeller® series SL4 LED multistrobe light, white 24V

PRODUCT NAME	Eaton Moeller® series SL4 Multi-strobe light module
CATALOG NUMBER	171376
PRODUCT LENGTH/DEPTH	43 mm
PRODUCT HEIGHT	75 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	0.042 kg
CERTIFICATIONS	UL UL report applies to both US and Canada CSA-C22.2 No. 14-10 UL 508 CE CSA-C22.2 No. 94-91 UL File No.: E29184 UL Category Control No.: NKCR CSA Class No.: NKCR7 Certified by UL for use in Canada IEC/EN 60529 IEC/EN 60947-5-1

TYPE	<ul style="list-style-type: none"> <li>• LED for effective signaling effect</li> <li>• Multi-strobe light module</li> </ul>
PRODUCT CATEGORY	SL signal towers
FEATURES	Various strobe sequences
POLLUTION DEGREE	3
FLASHING FREQUENCY	1 - 2.6 Hz
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V AC
ENCLOSURE COLOR	Black
FUNCTIONS	Flash light
COLOR	Other
VOLTAGE TYPE	AC/DC
MATERIAL	Cap: Polycarbonate (PC) Enclosure: Polycarbonate (PC)
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 13
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CURRENT CONSUMPTION	max. 165 mA at 24 V AC/DC
LIFESPAN, ELECTRICAL	100,000 h
LIGHT TYPE	Multistrobe light
LIGHT MODULES	LED
NUMBER OF MODULES	Max. 5 (with standard base) Max. 10 (with base for mounting on both sides)
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to

DECLARATIONS OF CONFORMITY	<a href="#">DA-DC-00004253.pdf</a>
	<a href="#">DA-DC-00004257.pdf</a>
	<a href="#">IL047001ZU</a>
	<a href="#">eaton-operating-sl4-continuous-light-dimensions.eps</a>
	<a href="#">eaton-operating-sl4-multi-strobe-light-module-symbol.eps</a>
	<a href="#">eaton-operating-button-sl7-continuous-light-symbol-003.eps</a>

<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	24 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN</b>	24 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX</b>	24 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN</b>	24 V
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	60 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-30 °C
<b>LEAKAGE CURRENT</b>	0.003 A
<b>OUTSIDE DIAMETER</b>	43 mm
<b>RADIATION ANGLE</b>	360 °
<b>RATED INSULATION VOLTAGE (UI)</b>	250 V

---

**PROJECT NAME:**

---

**PROJECT NUMBER:**

---

**PREPARED BY:**

---

: