

Eaton 170M6615

Fuse-link, high speed, 1100 A, AC 690 V, size 3, 76 x 92 x 135 mm, aR, IEC, UL

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6615
UPC	051712264839
PRODUCT LENGTH/DEPTH	170 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	96 mm
PRODUCT WEIGHT	1194 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	1100 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	91.3 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CLASS	Class aR
CLEARING (I2T)	1300000 at 660 V
WATT LOSSES	130 W
FUSE SHAPE	Square body, center bolted tags
PRE ARC (I2T)	190000
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	US Style FU/Without indicator Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

